

SlimShaper PRO

RPM: 500
TORQUE: 3

TAPER

Ø

ZS1



6-2%

15

ZS2



3-4%

20

ZS3



3-4%

25

GENERAL CHARACTERISTICS

Continuous rotating • Integrated conductivity • Minimally invasive system •
Integrated DualWire® technology

SlimShaper PRO



KFile

#10

Glide Path



ZS1

RPM: 500
Torque: 3

Shaping



ZS2

ZS3

RPM: 500
Torque: 3

Finishing



Irrigate, recapitulate with
a 10 file and re-irrigate
after removing each
rotary file